



# Systemdiagramm KL 200

**Order No. 158 340**  
Foot  $\varnothing = 100$  mm  
connecting thread M6



**Order No. 158 345**  
Knee joint L = 200 mm  
connecting thread M6



**Order No. 158 341**  
Mount for focusing  
attachment



**Order No. 158 330**  
Adapter for flexible  
light guide



**Order No. 158 210**  
Focusing attachment



**Order No. 158 210**  
Focusing attachment



**Order No. 158 211**  
Conversion filter



**Order No. 158 205**  
Polarisation filter




**Order No. 158 200**  
Focusing attachment  
and filter set



**Order No. 120 100**  
(230 V) KL 200

**Order No. 120 101**  
(120 V) KL 200



**Order No. 121 101**  
Flexible light guide 1-arm  
4.5 mm optic fiber bundle, 600 mm

**Order No. 171 101**  
Flexible light guide 1-arm  
4.5 mm optic fiber bundle, 1000 mm

**Order No. 171 202**  
Flexible light guide 2-arms  
4.0 mm optic fiber bundle, 1000 mm

**Order No. 170 101**  
Swan-neck light guide 1-arm  
3.5 mm optic fiber bundle, 500 mm

**Order No. 170 202**  
Swan-neck light guide 2-arms  
3.5 mm optic fiber bundle, 500 mm

**Order No. 172 501**  
6-point ring light,  $\varnothing_1 = 58$  mm  
flexible length 900 mm

**Order No. 172 601**  
6-point ring light,  $\varnothing_1 = 66$  mm  
flexible length 900 mm

**Order No. 122 150**  
Transmitted light stage;  
mounting diameter 84 mm,  
for flexible light guide up to  $\varnothing 5$  mm

